


 $a \cdot light$





FOLLOWING LIGHT Why compromise when you can adapt the lighting to its environment? ALOFT can be fine-tuned on-site to make last minute changes.







LINEAR SEGMENTS

Each linear segment of ALOFT can be specified with a different light option creating unique looks that can be adjusted to any environment.



BAFFLED OPTIC

Offered with 22° or 55° beam angles (FWHM), the baffled optic offers a precises cut-off angle and recessed cell-lens technology to maintain a discreet and minimal presence.

HE TECH™

The proprietary HE Tech™ provides high performance and excellent light distribution from a narrow 1/2" aperture diffuse lens.

DIFFUSE LENS

Delivering beautifully refined light with uncompromised performance, the diffuse lens is used for a wider lambertian distribution.

NO LIGHT

Unlit segments to bridge the gap between lit sections.



